

RackPower Basic PDU, RB0xxx, 230/400 VAC, 3-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

MERKMALE

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Produkttyp	Typ Buchse	Farbe	Länge	Spannung AC	Tiefe
RB0450	Buchsenleiste	IEC C13, IEC C13/C19	Schwarz	1490 mm	230 V	55 mm
RB0850	Buchsenleiste	IEC C13, IEC C13/C19	Schwarz	1780 mm	230 V	55 mm

Table 2/2

Katalognummer	Breite
RB0450	56 mm
RB0850	56 mm

ZUSÄTZLICHE PRODUKTDDETAILS

Please order bracket for vertical mounting separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE