

RackPower PDU, RP1xxx, 230/400 VAC, 3-phase

Energieversorger

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

EIGENSCHAFTEN

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6" with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Product Type	Socket Type	Farbe	Länge	Wechselspannung	Funktion
RP1450	Socket Strip	IEC C13, IEC C13/C19	Schwarz	1490 mm	230 V	Input Monitored
RP1850	Socket Strip	IEC C13, IEC C13/C19	Schwarz	1780 mm	230 V	Input Monitored
RP1950	Socket Strip	IEC C13, IEC C13/C19	Schwarz	1826 mm	230 V	Input Monitored

Table 2/2

Katalognummer	Tiefe	Breite
RP1450	55 mm	56 mm
RP1850	55 mm	56 mm
RP1950	75 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE