

nVent LENTON Interlok HYA15HT Grout Additive, Hot Temperature



The nVent LENTON HYA15LM Grout Additive, Hot Temperature is designed to be used in conjunction with nVent LENTON Interlok grout-fill couplers and nVent LENTON Interlok HY15LM Grout. The additive is used to increase working time of the grout during hot temperature applications which allows for a longer time window to place the grout into the Interlok couplers. This proprietary grout additive increases the maximum working temperature of HY15LM grout from 100 °F (38 °C) to 122 °F (50 °C).

MERKMALE

Allows for hot temperature grouting

Increases grout working time in hot climates

Extends the construction season

For use in pump or gravity fill applications

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Druckfestigkeit	Arbeitstemperatur	Stückgewicht
HYA15HT	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	21 to 50 °C	0.05 kg

ZUSÄTZLICHE PRODUKTDDETAILS

For use with HY15LM grout only.

Hot weather concreting procedures, such as ACI 305 Hot Weather Concreting, must be followed.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

HYA15HT can be used in temperatures as low as 70 °F (21 °C) to extend working time; however, this may slow the compressive strength curve.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Unser starkes markenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE