

19" Fan Unit, 1 U, Speed Control and Monitoring

Energieversorger

Fan Unit for installation into a 1 U space within the Cabinet.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Input Voltage AC	Input Voltage DC	Zertifizierungen
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Katalognummer	Input Voltage AC	Input Voltage DC	Zertifizierungen
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE