


Horizontal Rail Rear, Type AB for Rear I/O Board Guides, 84 HP

Power Utilities

KATALOGNUMMER

34561-584



Combinations of horizontal rails and side panels

	Light r.1	Standard r.2	Heavy r.3	Rugged r.4
Support r.1	-	+	+	+
Panel r.1	+	+	+	+
Panel r.2	+	+	+	+
Horizontal rail	+	+	-	-
Side panel	Light r.1	Standard r.2	Heavy r.3	Rugged r.4

Legend: "+" can be combined, "-" combination not recommended

Aluminum extrusion horizontal rail of the type AB (AB = support), for rear I/O card guides, with an anodized surface and conductive contact surface. Suitable for RatiopacPRO/-AIR and EuropacPRO/-rugged).

ZERTIFIZIERUNGEN



MERKMALE

For CompactPCI in the area of rear I/O

For 2 x 3 U expansion, 2 horizontal rails of type AB are required

Aluminum extrusion, anodized surface, conductive contact surface, without HP markings

PRODUKTMERKMALE

Produkttyp: Modulschiene

Produktfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Typ: Typ AB

Breite Gestell: 84 HP

Länge: 431.8 mm

Anzahl Verpackungen: 1

ZUSÄTZLICHE PRODUKTDDETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE