


EuropacPRO 19" Subrack Kit for Backplane, Shielded

Energieversorger

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

SPEZIFIKATIONEN

Product Type: Subrack/Chassis

Table 1/2

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/2

Katalognummer	Handle Included	Montage	Konform mit	EMC Shielding	Rack Width	Statische Last
24563-142	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-143	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-144	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-145	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

Katalognummer	HandleIncluded	Montage	Konform mit	EMC Shielding	Rack Width	Statische Last
24563-146	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-442	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-443	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-444	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-445	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf
24563-446	Nein	Rack	IEC 60297-3-103	Ja	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE