

Front Panel, Anodized With Untreated Edges, Unshielded

Energieversorger



Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-271	2 U	84 HP	1	Keine	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Keine	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-331	3 U	63 HP	1	Keine	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Keine	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Keine	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Keine	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Keine	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Keine	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Keine	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Keine	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Keine	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Keine	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Keine	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Keine	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Keine	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Keine	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Keine	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Keine	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Keine	Screw-on Front	Anodized
30818-284	3 U	16 HP		Keine	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30818-289	3 U	21 HP	5	Keine	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Keine	Screw-on Front	Anodized
30818-517	6 U	3 HP		Keine	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Keine	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Keine	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Keine	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Keine	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Keine	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Keine	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Keine	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Keine	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Keine	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Keine	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Keine	Screw-on Front	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30818-271	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium
30818-310	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30818-331	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-352	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-434	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium
30818-556	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-577	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-598	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30810-433	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-747	Anodized	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-272	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-273	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-274	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-275	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-276	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-277	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30818-279	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-281	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-282	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-284	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-289	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-296	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30818-517	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-518	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-519	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-520	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-521	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-522	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-524	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-526	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30818-528	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-530	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-535	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30818-542	Anodized	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30818-271	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30818-310	Frontplatte	Front Panel without Handle	213 mm	RoHS
30818-331	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
30818-352	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30818-434	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30818-556	Frontplatte	Front Panel without Handle	213 mm	RoHS
30818-577	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
30818-598	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30810-433	Frontplatte	Front Panel without Handle	9.8 mm	RoHS
30818-747	Frontplatte	Front Panel without Handle	9.8 mm	RoHS
30818-272	Frontplatte	Front Panel without Handle	14.9 mm	RoHS
30818-273	Frontplatte	Front Panel without Handle	20 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30818-274	Frontplatte	Front Panel without Handle	25 mm	RoHS
30818-275	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30818-276	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30818-277	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30818-279	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30818-281	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30818-282	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
30818-284	Frontplatte	Front Panel without Handle	80.9 mm	
30818-289	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
30818-296	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
30818-517	Frontplatte	Front Panel without Handle	14.9 mm	
30818-518	Frontplatte	Front Panel without Handle	20 mm	RoHS
30818-519	Frontplatte	Front Panel without Handle	25 mm	RoHS
30818-520	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30818-521	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30818-522	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30818-524	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30818-526	Frontplatte	Front Panel without Handle	60.6 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30818-528	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
30818-530	Frontplatte	Front Panel without Handle	80.9 mm	RoHS
30818-535	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
30818-542	Frontplatte	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE