

Front Panel, Front Anodized, Rear Conductive, Unshielded

Energieversorger

Front panel, unshielded, front anodized and rear conductive.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30838-123	3 U	84 HP	1	Keine	Screw-on Front	Anodized
30838-204	6 U	84 HP	1	Keine	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30847-465	4 U	84 HP	1	Keine	Screw-on Front	Anodized
30847-469	5 U	84 HP	1	Keine	Screw-on Front	Anodized
30847-461	2 U	84 HP	1	Keine	Screw-on Front	Anodized
30838-081	3 U	42 HP	1	Keine	Screw-on Front	Anodized
30838-102	3 U	63 HP	1	Keine	Screw-on Front	Anodized
30838-162	6 U	42 HP	1	Keine	Screw-on Front	Anodized
30838-183	6 U	63 HP	1	Keine	Screw-on Front	Anodized
30847-459	2 U	42 HP	1	Keine	Screw-on Front	Anodized
30847-460	2 U	63 HP	1	Keine	Screw-on Front	Anodized
30847-463	4 U	42 HP	1	Keine	Screw-on Front	Anodized
30847-464	4 U	63 HP	1	Keine	Screw-on Front	Anodized
30847-467	5 U	42 HP	1	Keine	Screw-on Front	Anodized
30847-468	5 U	63 HP	1	Keine	Screw-on Front	Anodized
30847-458	2 U	28 HP	5	Keine	Screw-on Front	Anodized
30847-470	3 U	2 HP	5	Keine	Screw-on Front	Anodized
30838-067	3 U	28 HP	5	Keine	Screw-on Front	Anodized
30838-043	3 U	4 HP	5	Keine	Screw-on Front	Anodized
30838-044	3 U	5 HP	5	Keine	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30838-045	3 U	6 HP	5	Keine	Screw-on Front	Anodized
30838-046	3 U	7 HP	5	Keine	Screw-on Front	Anodized
30838-047	3 U	8 HP	5	Keine	Screw-on Front	Anodized
30838-049	3 U	10 HP	5	Keine	Screw-on Front	Anodized
30838-051	3 U	12 HP	5	Keine	Screw-on Front	Anodized
30838-053	3 U	14 HP	5	Keine	Screw-on Front	Anodized
30838-055	3 U	16 HP		Keine	Screw-on Front	Anodized
30838-060	3 U	21 HP	5	Keine	Screw-on Front	Anodized
30847-471	3 U	3 HP	5	Keine	Screw-on Front	Anodized
30847-476	4 U	4 HP	5		Screw-on Front	Anodized
30847-462	4 U	28 HP	5	Keine	Screw-on Front	Anodized
30838-124	6 U	4 HP	5	Keine	Screw-on Front	Anodized
30847-466	5 U	28 HP	5	Keine	Screw-on Front	Anodized
30838-125	6 U	5 HP	5	Keine	Screw-on Front	Anodized
30838-126	6 U	6 HP	5	Keine	Screw-on Front	Anodized
30838-127	6 U	7 HP	5	Keine	Screw-on Front	Anodized
30838-128	6 U	8 HP	5	Keine	Screw-on Front	Anodized
30838-130	6 U	10 HP	5	Keine	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montage	Front Finish
30838-132	6 U	12 HP	5	Keine	Screw-on Front	Anodized
30838-134	6 U	14 HP	5	Keine	Screw-on Front	Anodized
30838-136	6 U	16 HP	5	Keine	Screw-on Front	Anodized
30838-141	6 U	21 HP	5	Keine	Screw-on Front	Anodized
30838-148	6 U	28 HP	5	Keine	Screw-on Front	Anodized
30847-480	9 U	8 HP	5		Screw-on Front	Anodized
30847-482	9 U	10 HP	5		Screw-on Front	Anodized
30847-484	9 U	12 HP	5		Screw-on Front	Anodized
30847-556	9 U	84 HP	5	Keine	Screw-on Front	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30838-123	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-204	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30847-465	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium
30847-469	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	217.4 mm	Aluminium
30847-461	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium
30838-081	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30838-102	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-162	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-183	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30847-459	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium
30847-460	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium
30847-463	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium
30847-464	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium
30847-467	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	217.4 mm	Aluminium
30847-468	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	217.4 mm	Aluminium
30847-458	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium
30847-470	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-067	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-043	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-044	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30838-045	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-046	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-047	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-049	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-051	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-053	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-055	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30838-060	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30847-471	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium
30847-476	Conductive	Nein		Nein	395.1 mm	Aluminium
30847-462	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium
30838-124	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30847-466	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	217.4 mm	Aluminium
30838-125	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30838-126	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-127	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-128	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-130	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-132	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-134	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-136	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-141	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30838-148	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium
30847-480	Conductive	Nein		Nein	395.1 mm	Aluminium
30847-482	Conductive	Nein		Nein	395.1 mm	Aluminium
30847-484	Conductive	Nein		Nein	395.1 mm	Aluminium
30847-556	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	395.1 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30838-123	Frontplatte	Front Panel without Handle	426.4 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30838-204	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30847-465	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30847-469	Frontplatte	Front Panel without Handle	426.4 mm	
30847-461	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
30838-081	Frontplatte	Front Panel without Handle	213 mm	RoHS
30838-102	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
30838-162	Frontplatte	Front Panel without Handle	213 mm	RoHS
30838-183	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
30847-459	Frontplatte	Front Panel without Handle	213 mm	
30847-460	Frontplatte	Front Panel without Handle	319.7 mm	
30847-463	Frontplatte	Front Panel without Handle	213 mm	RoHS
30847-464	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
30847-467	Frontplatte	Front Panel without Handle	213 mm	
30847-468	Frontplatte	Front Panel without Handle	319.7 mm	
30847-458	Frontplatte	Front Panel without Handle	141.9 mm	
30847-470	Frontplatte	Front Panel without Handle	9.8 mm	RoHS
30838-067	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
30838-043	Frontplatte	Front Panel without Handle	20 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30838-044	Frontplatte	Front Panel without Handle	25 mm	RoHS
30838-045	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30838-046	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30838-047	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30838-049	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30838-051	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30838-053	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
30838-055	Frontplatte	Front Panel without Handle	80.9 mm	RoHS
30838-060	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
30847-471	Frontplatte	Front Panel without Handle	14.9 mm	RoHS
30847-476	Frontplatte	Front Panel without Handle	20 mm	RoHS
30847-462	Frontplatte	Front Panel without Handle	141.9 mm	
30838-124	Frontplatte	Front Panel without Handle	20 mm	RoHS
30847-466	Frontplatte	Front Panel without Handle	141.9 mm	
30838-125	Frontplatte	Front Panel without Handle	25 mm	RoHS
30838-126	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30838-127	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30838-128	Frontplatte	Front Panel without Handle	40.3 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30838-130	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30838-132	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30838-134	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
30838-136	Frontplatte	Front Panel without Handle	80.9 mm	RoHS
30838-141	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
30838-148	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
30847-480	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30847-482	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30847-484	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30847-556	Frontplatte	Front Panel without Handle	426.4 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE