


Novastar Raised Top Cover

Energieversorger



Raised top cover for better ventilation and heat escape.
Novastar raised top cover is robust and not dismountable from the outside.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Raised Top cover (31 mm) with all-round air gap of 10 mm

Top cover attached from the inside (no screws on the outside)

Suitable for placing heavy parts on the top cover

Incl. grounding

Robust version, load-carrying capacity 50 kg

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Tiefe	Farbe	Color Code	Product Type	Typ	Breite
25230-039	500 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-142	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm

Katalognummer	Tiefe	Farbe	Color Code	Product Type	Typ	Breite
25230-037	800 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-141	900 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-038	600 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm

ADDITIONAL PRODUCT DETAILS

Please order lifting eye separately if required.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE