

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding

Energieversorger



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets for assembly into a 19" rack.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Retrofittable EMC shielding

Version with 19" mounting brackets

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

Symmetrical design, identical front and rear side

No visible screws; cladding parts removable without tools

Conforms with DIN EN 62368-1

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-438	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-441	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-442	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-443	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-444	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-486	4 U	255.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-489	4 U	315.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-490	4 U	375.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-491	4 U	435.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-492	4 U	495.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-534	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-537	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-538	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24571-539	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Katalognummer	Rack Height	Tiefe	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24571-540	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-201	5 U	255.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-204	5 U	315.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-205	5 U	375.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-206	5 U	435.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-207	5 U	495.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-345	5 U	255.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-348	5 U	315.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-349	5 U	375.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-350	5 U	435.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-351	5 U	495.5 mm	1	201.25 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-570	2 U	255.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-573	2 U	315.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-574	2 U	375.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Katalognummer	Rack Height	Tiefe	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-575	2 U	435.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails
24572-576	2 U	495.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets, Horizontal Rails

Table 2/3

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
24571-438	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24571-441	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24571-442	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24571-443	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24571-444	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24571-486	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
24571-489	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24571-490	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24571-491	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24571-492	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24571-534	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24571-537	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24571-538	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
24571-539	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24571-540	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24572-201	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-204	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-205	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-206	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-207	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
24572-345	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-348	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-349	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-350	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-351	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	221.5 mm	RatiopacPRO	Gehäuse
24572-570	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-573	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
24572-574	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-575	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-576	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse

Table 3/3

Katalognummer	Protection Rating	Rack Width	Statische Last	Typ	Breite
24571-438	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-441	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-442	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-443	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-444	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-486	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-489	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-490	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Katalognummer	Protection Rating	Rack Width	Statische Last	Typ	Breite
24571-491	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-492	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-534	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-537	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-538	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-539	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24571-540	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-201	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-204	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-205	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-206	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-207	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-345	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-348	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-349	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Katalognummer	Protection Rating	Rack Width	Statische Last	Typ	Breite
24572-350	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-351	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-570	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-573	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-574	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-575	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-576	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE