

Varistar CP Bottom Rear Panel, Shortened

Energieversorger

Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

EIGENSCHAFTEN

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Protection Rating	Farbe	Color Code
21630-354	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-355	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-356	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-357	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-358	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-359	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Katalognummer	Product Type
21630-354	Cabinet Door

Katalognummer	Product Type
21630-355	Cabinet Door
21630-356	Cabinet Door
21630-357	Cabinet Door
21630-358	Cabinet Door
21630-359	Cabinet Door

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE