

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC

Energieversorger

Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the [Online Configurator](#)

EIGENSCHAFTEN

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Statische Belastungskapazität 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Frame Material	Rack Height	Höhe	Breite	Tiefe	Statische Last
10630-048	Stahl	42 U	2000 mm	600 mm	800 mm	1600 kgf

Table 2/3

Katalognummer	Protection Rating	Konform mit	Farbe	Color Code	Material	Shock and Vibration Tolerance
---------------	-------------------	-------------	-------	------------	----------	-------------------------------

10630-048	IP55	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3, IEC 61587-1, IEC 61587-2, EN 45545-2	Black Grey	RAL 7021	Stahl	5 g (force)
-----------	------	--	------------	----------	-------	-------------

Table 3/3

Katalognummer	Kompatibel mit
10630-048	Varistar CP

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE