

# Varistar CP Steel Door, Perforated With 1-Point Locking

## Energieversorger

Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

### EIGENSCHAFTEN

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

### SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Rack Height | Höhe    | Breite | Locking Type         | Farbe      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-408     | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-409     | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-507     | 24 U        | 1200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-508     | 24 U        | 1200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-410     | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-411     | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-509     | 29 U        | 1400 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| Katalognummer | Rack Height | Höhe    | Breite | Locking Type         | Farbe      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-510     | 29 U        | 1400 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-412     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-413     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-511     | 33 U        | 1600 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-512     | 33 U        | 1600 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-414     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-415     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-513     | 38 U        | 1800 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-514     | 38 U        | 1800 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-006     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-013     | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-515     | 42 U        | 2000 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-516     | 42 U        | 2000 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-007     | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-014     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-517     | 47 U        | 2200 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-518     | 47 U        | 2200 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |
| 21630-008     | 52 U        | 2450 mm | 600 mm | Single Point Locking | Black Grey | RAL 7021   |

| Katalognummer | Rack Height | Höhe    | Breite | Locking Type         | Farbe      | Color Code |
|---------------|-------------|---------|--------|----------------------|------------|------------|
| 21630-015     | 52 U        | 2450 mm | 800 mm | Single Point Locking | Black Grey | RAL 7021   |

Table 2/2

| Katalognummer | Konform mit              | Product Type | Protection Rating | Typ                    | Kompatibel mit |
|---------------|--------------------------|--------------|-------------------|------------------------|----------------|
| 21630-408     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-409     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-507     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-508     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-410     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-411     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-509     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-510     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-412     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-413     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-511     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-512     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-414     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-415     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-513     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-514     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |

| Katalognummer | Konform mit              | Product Type | Protection Rating | Typ                    | Kompatibel mit |
|---------------|--------------------------|--------------|-------------------|------------------------|----------------|
| 21630-006     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-013     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-515     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-516     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-007     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-014     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-517     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-518     | IEC 61587-1              | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-008     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |
| 21630-015     | IEC 61587-1, IEC 61587-3 | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP    |

## ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**