

Varistar CP Steel Door, Perforated With 3-Point Locking

Energieversorger

Varistar CP perforated steel door 3-point locking for IP 20 applications.

EIGENSCHAFTEN

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-098	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-099	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-100	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-101	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-102	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-103	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-424	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-425	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-426	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-427	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-428	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-429	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-430	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-431	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Katalognummer	Locking Type	Product Type	Protection Rating	Typ	Kompatibel mit
21630-098	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-099	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-100	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-101	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-102	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-103	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-424	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-425	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-426	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-427	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

Katalognummer	Locking Type	Product Type	Protection Rating	Typ	Kompatibel mit
21630-428	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-429	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-430	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-431	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE