

ACS-30 User Interface Terminal



nVent RAYCHEM ACS-UIT3 is a user interface terminal used together with the ACS-PCM2-5 panel in the ACS-30 system. With large LCD touch-screen display, it provides easy programming without keyboards or cryptic labels.

MERKMALE

Simple to install and operate, with large touch screen display

Alarm outputs

Multiple communications ports (RS-485, RS-232, or 10/100Base-T Ethernet)

BACnet to Modbus protocol gateways, with Modbus registries pre-programmed

USB interface, for easy configuration and firmware upgrades

Reliable during long life: 2 year product warranty available, maintenance free

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Artikelname	Versorgungsspannung	Display	Material	Schutzart	Höhe
10332-039	ACS-UIT3 REPLACEMENT UNIT	10 – 36 V	12-Zoll-Touchscreen, TFT-LCD	FRP	IP20	245 mm
1244-022626	ACS-30-EU-UIT3	100 – 240 V	12-Zoll-Touchscreen, TFT-LCD	FRP	IP65	400 mm

Table 2/2

Katalognummer	Artikelname	Breite	Tiefe
10332-039	ACS-UIT3 REPLACEMENT UNIT	306 mm	63 mm

Katalognummer	Artikelname	Breite	Tiefe
1244-022626	ACS-30-EU-UIT3	400 mm	210 mm

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Unser starkes markenportfolio:

RAYCHEM PYROTENAX TRACER NUHEAT