

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

KATALOGNUMMER

34566-284



Combinations of horizontal rails and side panels

	Light r.d.	Frontier f.	Heavy r.d.	Rugged r.d.
Heavy r.d.	-	+	+	+
Frontier f.	+	+	+	+
Light r.d.	+	+	-	-
Rugged r.d.	+	+	-	-

Legend: + can be combined, - combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

ZERTIFIZIERUNGEN



MERKMALE

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUKTMERKMALE

Produkttyp: Modulschiene

Produktfamilie: EuropacPRO

Typ: Robust, KD

Breite Gestell: 84 HP

Länge: 431.8 mm

ZUSÄTZLICHE PRODUKTDDETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE