

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Energieversorger

Rear horizontal rail for backplane mounting with insulation strip



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montage	Konform mit	EMC Shielding	Product Type
24563-161	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-162	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-163	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-164	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-461	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-462	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-463	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	HandleIncluded	Montage	Konform mit	EMC Shielding	Product Type
24563-464	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statische Last
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE