

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Energieversorger

Non-shielded subrack for backplane mounting.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-131	3 U	175 mm	1	Backplane	160 mm	Edelstahl
24563-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Edelstahl
24563-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Edelstahl
24563-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-135	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-136	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-431	6 U	175 mm	1	Backplane	160 mm	Edelstahl
24563-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Edelstahl
24563-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Edelstahl
24563-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-435	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-436	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl

Table 2/3

Katalognummer	Handle Included	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24563-131	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-132	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Katalognummer	HandleIncluded	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24563-133	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-134	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-135	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-136	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-431	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-432	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-433	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-434	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-435	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-436	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statische Last
24563-131	11 kgf
24563-132	11 kgf
24563-133	11 kgf
24563-134	11 kgf
24563-135	11 kgf
24563-136	11 kgf
24563-431	11 kgf

Katalognummer	Statische Last
24563-432	11 kgf
24563-433	11 kgf
24563-434	11 kgf
24563-435	11 kgf
24563-436	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE