

Fan Unit With Housing for 19" Pusher Fan, 2 U, Axial

Energieversorger

Supplementary fan (built-on) with housing for Schroff pusher fan 2 U. No additional voltage supply necessary: connection is via 19" pusher fan.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Extra 2 U useable space: by using a built-on fan, components mounted below the 19" pusher fan can be cooled

No additional voltage supply necessary: connection is via 19" pusher fan, 2 U

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Typ	Farbe	Input Voltage AC
10713-530	Lüftereinschub	Silver	230 V min

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE