

Front Panel, Flat, With Slot for Stainless Steel EMC Gasket

Energieversorger

Front panel, flat, with slot for stainless steel EMC gasket.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish	Treated Edges
30846-682	63 HP	1	Screw-on Front			
30846-681	42 HP	1	Screw-on Front	Anodized	Conductive	Nein

Table 2/2

Katalognummer	Höhe	Material	Product Type	Rack Height	Typ	Breite
30846-682	172.9 mm	Aluminium	Frontplatte	4 U	Front Panel without Handle	319.7 mm
30846-681	172.9 mm	Aluminium	Frontplatte	4 U	Front Panel without Handle	213 mm

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE