

Front Panel, Retrofit Shielding

Energieversorger



Flat front panel. Shieldable with stainless steel EMC gasket.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20846-437	3 U	42 HP	1	Screw-on Front	Edelstahl	Anodized
20846-438	3 U	63 HP	1	Screw-on Front	Edelstahl	Anodized
20846-453	6 U	42 HP	1	Screw-on Front	Edelstahl	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20846-454	6 U	63 HP	1	Screw-on Front	Edelstahl	Anodized
30846-676	3 U	84 HP	1	Screw-on Front	Edelstahl	Anodized
30846-683	4 U	84 HP	1	Screw-on Front	Edelstahl	Anodized
30846-771	6 U	84 HP	1	Screw-on Front	Edelstahl	Anodized
30846-859	9 U	84 HP	1	Screw-on Front	Edelstahl	Anodized
30846-588	2 U	84 HP	1	Screw-on Front	Edelstahl	Anodized
30846-864	3 U	2 HP	5	Screw-on Front	Edelstahl	Anodized
30846-865	6 U	2 HP	5	Screw-on Front	Edelstahl	Anodized
20846-424	3 U	16 HP		Screw-on Front	Edelstahl	Anodized
20846-425	3 U	3 HP	5	Screw-on Front	Edelstahl	Anodized
20846-426	3 U	4 HP	5	Screw-on Front	Edelstahl	Anodized
20846-427	3 U	5 HP	5	Screw-on Front	Edelstahl	Anodized
20846-428	3 U	6 HP	5	Screw-on Front	Edelstahl	Anodized
20846-429	3 U	7 HP	5	Screw-on Front	Edelstahl	Anodized
20846-430	3 U	8 HP	5	Screw-on Front	Edelstahl	Anodized
20846-431	3 U	10 HP	5	Screw-on Front	Edelstahl	Anodized
20846-432	3 U	12 HP	5	Screw-on Front	Edelstahl	Anodized
20846-433	3 U	14 HP	5	Screw-on Front	Edelstahl	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20846-434	3 U	21 HP	5	Screw-on Front	Edelstahl	Anodized
20846-436	3 U	28 HP	5	Screw-on Front	Edelstahl	Anodized
20846-442	6 U	3 HP		Screw-on Front	Edelstahl	Anodized
20846-443	6 U	4 HP	5	Screw-on Front	Edelstahl	Anodized
20846-444	6 U	5 HP	5	Screw-on Front	Edelstahl	Anodized
20846-445	6 U	6 HP	5	Screw-on Front	Edelstahl	Anodized
20846-446	6 U	7 HP	5	Screw-on Front	Edelstahl	Anodized
20846-447	6 U	8 HP	5	Screw-on Front	Edelstahl	Anodized
20846-448	6 U	10 HP	5	Screw-on Front	Edelstahl	Anodized
20846-449	6 U	12 HP	5	Screw-on Front	Edelstahl	Anodized
20846-450	6 U	14 HP	5	Screw-on Front	Edelstahl	Anodized
20846-451	6 U	21 HP	5	Screw-on Front	Edelstahl	Anodized
20846-452	6 U	28 HP	5	Screw-on Front	Edelstahl	Anodized
20846-456	6 U	16 HP	5	Screw-on Front	Edelstahl	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20846-437	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-438	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20846-453	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-454	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30846-676	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30846-683	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
30846-771	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30846-859	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	395.1 mm	Aluminium
30846-588	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
30846-864	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30846-865	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-424	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-425	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-426	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-427	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-428	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20846-429	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-430	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-431	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-432	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-433	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-434	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-436	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-442	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-443	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-444	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-445	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-446	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-447	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-448	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20846-449	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-450	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-451	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-452	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-456	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Breite
20846-437	Frontplatte	Front Panel without Handle	213 mm
20846-438	Frontplatte	Front Panel without Handle	319.7 mm
20846-453	Frontplatte	Front Panel without Handle	213 mm
20846-454	Frontplatte	Front Panel without Handle	319.7 mm
30846-676	Frontplatte	Front Panel without Handle	426.4 mm
30846-683	Frontplatte	Front Panel without Handle	426.4 mm
30846-771	Frontplatte	Front Panel without Handle	426.4 mm
30846-859	Frontplatte	Front Panel without Handle	426.4 mm
30846-588	Frontplatte	Front Panel without Handle	426.4 mm
30846-864	Frontplatte	Front Panel without Handle	9.8 mm

Katalognummer	Product Type	Typ	Breite
30846-865	Frontplatte	Front Panel without Handle	9.8 mm
20846-424	Frontplatte	Front Panel without Handle	80.9 mm
20846-425	Frontplatte	Front Panel without Handle	14.9 mm
20846-426	Frontplatte	Front Panel without Handle	20 mm
20846-427	Frontplatte	Front Panel without Handle	25 mm
20846-428	Frontplatte	Front Panel without Handle	30.1 mm
20846-429	Frontplatte	Front Panel without Handle	35.2 mm
20846-430	Frontplatte	Front Panel without Handle	40.3 mm
20846-431	Frontplatte	Front Panel without Handle	50.5 mm
20846-432	Frontplatte	Front Panel without Handle	60.6 mm
20846-433	Frontplatte	Front Panel without Handle	70.8 mm
20846-434	Frontplatte	Front Panel without Handle	106.3 mm
20846-436	Frontplatte	Front Panel without Handle	141.9 mm
20846-442	Frontplatte	Front Panel without Handle	14.9 mm
20846-443	Frontplatte	Front Panel without Handle	20 mm
20846-444	Frontplatte	Front Panel without Handle	25 mm
20846-445	Frontplatte	Front Panel without Handle	30.1 mm
20846-446	Frontplatte	Front Panel without Handle	35.2 mm

Katalognummer	Product Type	Typ	Breite
20846-447	Frontplatte	Front Panel without Handle	40.3 mm
20846-448	Frontplatte	Front Panel without Handle	50.5 mm
20846-449	Frontplatte	Front Panel without Handle	60.6 mm
20846-450	Frontplatte	Front Panel without Handle	70.8 mm
20846-451	Frontplatte	Front Panel without Handle	106.3 mm
20846-452	Frontplatte	Front Panel without Handle	141.9 mm
20846-456	Frontplatte	Front Panel without Handle	80.9 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE