


Front Panel, U-profile, Refrofit Shielding

Energieversorger



U-profile front panel for textile EMC gasket.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPEZIFIKATIONEN

Table 1/3						
Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20848-047	3 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-068	3 U	63 HP	1	Screw-on Front	Textile	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20848-097	3 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-139	6 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-160	6 U	63 HP	1	Screw-on Front	Textile	Anodized
20848-189	6 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-260	2 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-261	2 U	63 HP	1	Screw-on Front	Textile	Anodized
20848-262	2 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-268	4 U	28 HP	1	Screw-on Front	Textile	Anodized
20848-269	4 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-270	4 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-271	4 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-280	9 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-648	5 U	42 HP	1	Screw-on Front	Textile	Anodized
20848-649	5 U	63 HP	1	Screw-on Front	Textile	Anodized
20848-650	5 U	84 HP	1	Screw-on Front	Textile	Anodized
20848-206	2 U	28 HP	5	Screw-on Front	Textile	Anodized
30849-001	3 U	2 HP	5	Screw-on Front	Textile	Anodized
30849-002	6 U	2 HP	5	Screw-on Front	Textile	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20848-013	3 U	14 HP	5	Screw-on Front	Textile	Anodized
20848-015	3 U	16 HP	5	Screw-on Front	Textile	Anodized
20848-020	3 U	21 HP	5	Screw-on Front	Textile	Anodized
20848-027	3 U	28 HP	5	Screw-on Front	Textile	Anodized
30848-354	3 U	4 HP	5	Screw-on Front	Textile	Anodized
30848-356	3 U	8 HP	5	Screw-on Front	Textile	Anodized
30848-358	3 U	12 HP	5	Screw-on Front	Textile	Anodized
30848-378	3 U	5 HP	5	Screw-on Front	Textile	Anodized
30848-380	3 U	6 HP	5	Screw-on Front	Textile	Anodized
30848-382	3 U	7 HP	5	Screw-on Front	Textile	Anodized
30848-384	3 U	9 HP	5	Screw-on Front	Textile	Anodized
30848-385	3 U	9 HP	5	Screw-on Front	Textile	Anodized
30848-386	3 U	10 HP	5	Screw-on Front	Textile	Anodized
30849-004	3 U	3 HP	5	Screw-on Front	Textile	Anodized
30849-005	6 U	3 HP		Screw-on Front		Anodized
30848-355	6 U	4 HP	5	Screw-on Front	Textile	Anodized
20848-647	5 U	28 HP	5	Screw-on Front	Textile	Anodized
30848-379	6 U	5 HP	5	Screw-on Front	Textile	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	EMC Gasket Type	Front Finish
20848-106	6 U	14 HP	5	Screw-on Front	Textile	Anodized
20848-108	6 U	16 HP	5	Screw-on Front	Textile	Anodized
20848-113	6 U	21 HP	5	Screw-on Front	Textile	Anodized
20848-120	6 U	28 HP	5	Screw-on Front	Textile	Anodized
30848-357	6 U	8 HP	5	Screw-on Front	Textile	Anodized
30848-359	6 U	12 HP	5	Screw-on Front	Textile	Anodized
30848-381	6 U	6 HP	5	Screw-on Front	Textile	Anodized
30848-383	6 U	7 HP	5	Screw-on Front	Textile	Anodized
30848-387	6 U	10 HP	5	Screw-on Front	Textile	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20848-047	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-068	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-097	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-139	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-160	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-189	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20848-260	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
20848-261	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
20848-262	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
20848-268	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
20848-269	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
20848-270	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
20848-271	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
20848-280	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	395.1 mm	Aluminium
20848-648	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminium
20848-649	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminium
20848-650	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminium
20848-206	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
30849-001	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30849-002	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
20848-013	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-015	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-020	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20848-027	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-354	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-356	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-358	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-378	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-380	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-382	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-384	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30848-385	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-386	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30849-004	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Konform mit	EMC Shielding	Höhe	Material
30849-005	Conductive	Nein			261.8 mm	Aluminium
30848-355	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-647	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	217.4 mm	Aluminium
30848-379	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-106	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-108	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-113	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20848-120	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-357	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-359	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-381	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-383	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30848-387	Conductive	Nein	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
20848-047	Frontplatte	Front Panel without Handle	213 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
20848-068	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
20848-097	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
20848-139	Frontplatte	Front Panel without Handle	213 mm	RoHS
20848-160	Frontplatte	Front Panel without Handle	319.7 mm	RoHS
20848-189	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
20848-260	Frontplatte	Front Panel without Handle	213 mm	
20848-261	Frontplatte	Front Panel without Handle	319.7 mm	
20848-262	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
20848-268	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
20848-269	Frontplatte	Front Panel without Handle	213 mm	RoHS
20848-270	Frontplatte	Front Panel without Handle	213 mm	RoHS
20848-271	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
20848-280	Frontplatte	Front Panel without Handle	426.4 mm	RoHS
20848-648	Frontplatte	Front Panel without Handle	213 mm	
20848-649	Frontplatte	Front Panel without Handle	319.7 mm	
20848-650	Frontplatte	Front Panel without Handle	426.4 mm	
20848-206	Frontplatte	Front Panel without Handle	141.9 mm	
30849-001	Frontplatte	Front Panel without Handle	9.8 mm	RoHS

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30849-002	Frontplatte	Front Panel without Handle	9.8 mm	RoHS
20848-013	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
20848-015	Frontplatte	Front Panel without Handle	80.9 mm	RoHS
20848-020	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
20848-027	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
30848-354	Frontplatte	Front Panel without Handle	20 mm	RoHS
30848-356	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30848-358	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30848-378	Frontplatte	Front Panel without Handle	25 mm	RoHS
30848-380	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30848-382	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30848-384	Frontplatte	Front Panel without Handle	45.38 mm	
30848-385	Frontplatte	Front Panel without Handle	45.38 mm	
30848-386	Frontplatte	Front Panel without Handle	50.5 mm	RoHS
30849-004	Frontplatte	Front Panel without Handle	14.9 mm	RoHS
30849-005	Frontplatte	Front Panel without Handle	14.9 mm	
30848-355	Frontplatte	Front Panel without Handle	20 mm	RoHS
20848-647	Frontplatte	Front Panel without Handle	141.9 mm	

Katalognummer	Product Type	Typ	Breite	Zertifizierungen
30848-379	Frontplatte	Front Panel without Handle	25 mm	RoHS
20848-106	Frontplatte	Front Panel without Handle	70.8 mm	RoHS
20848-108	Frontplatte	Front Panel without Handle	80.9 mm	RoHS
20848-113	Frontplatte	Front Panel without Handle	106.3 mm	RoHS
20848-120	Frontplatte	Front Panel without Handle	141.9 mm	RoHS
30848-357	Frontplatte	Front Panel without Handle	40.3 mm	RoHS
30848-359	Frontplatte	Front Panel without Handle	60.6 mm	RoHS
30848-381	Frontplatte	Front Panel without Handle	30.1 mm	RoHS
30848-383	Frontplatte	Front Panel without Handle	35.2 mm	RoHS
30848-387	Frontplatte	Front Panel without Handle	50.5 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).

Differences in finish between 2 ... 12 HP and 14 ... 84 HP.

2 ... 12 HP: one-part U-profile

Please order textile EMC gasket separately.

Standard pack quantity: 2 to 28HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE