

Front Panel, Unshielded, Cut Outs for Coax Connectors

Energieversorger



Aluminum, 2.5 mm, front anodized, conductive, unshielded version.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Aluminum, 2.5 mm, front anodized, conductive

3 U, 4 HP

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Typ	Montage	EMC Shielding	Material	Front Finish	Rear Finish
30118-355	Front Panel without Handle	Screw-on Front	Nein	Aluminium	Anodized	Conductive

Table 2/3

Katalognummer	Treated Edges	Rack Height	Höhe	Rack Width	Breite	Konform mit
30118-355	Nein	3 U	128.4 mm	4 HP	20 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3

Katalognummer	Package Quantity
30118-355	5

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE