

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding With Handles

Energieversorger



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets and handles for assembly into a 19" rack.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with 19" mounting brackets with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

No visible screws; cladding parts removable without tools

Symmetrical design, identical front and rear side

Conforms with DIN EN 62368-1

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-620	2 U	255.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-623	2 U	315.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-624	2 U	375.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-625	2 U	435.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-626	2 U	495.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-630	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-633	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-634	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-635	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-636	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-640	4 U	255.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Katalognummer	Rack Height	Tiefe	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-643	4 U	315.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-644	4 U	375.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-645	4 U	435.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-646	4 U	495.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-660	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-663	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-664	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-665	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-666	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Table 2/3

Katalognummer	Cooling Option	Konform mit	EMC Shielding	Höhe	Product Family	Product Type
---------------	----------------	-------------	---------------	------	----------------	--------------

24572-620	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-623	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-624	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-625	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-626	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Gehäuse
24572-630	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24572-633	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24572-634	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse

24572-635	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24572-636	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Gehäuse
24572-640	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24572-643	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24572-644	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24572-645	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24572-646	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Gehäuse
24572-660	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse

24572-663	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24572-664	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24572-665	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse
24572-666	Nein	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Gehäuse

Table 3/3

Katalognummer	Protection Rating	Rack Width	Statische Last	Typ	Breite
24572-620	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-623	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-624	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-625	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-626	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-630	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Katalognummer	Protection Rating	Rack Width	Statische Last	Typ	Breite
24572-633	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-634	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-635	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-636	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-640	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-643	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-644	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-645	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-646	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-660	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-663	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-664	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-665	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-666	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE