

Varistar CP Steel Door, Perforated With Multi-Point Locking

Energieversorger

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

EIGENSCHAFTEN

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Katalognummer	Material	Product Type	Typ
21630-533	Stahl	Cabinet Door	Steel Door, Perforated
21630-534	Stahl	Cabinet Door	Steel Door, Perforated
21630-535	Stahl	Cabinet Door	Steel Door, Perforated
21630-536	Stahl	Cabinet Door	Steel Door, Perforated
21630-537	Stahl	Cabinet Door	Steel Door, Perforated
21630-538	Stahl	Cabinet Door	Steel Door, Perforated
21630-539	Stahl	Cabinet Door	Steel Door, Perforated
21630-540	Stahl	Cabinet Door	Steel Door, Perforated
21630-541	Stahl	Cabinet Door	Steel Door, Perforated
21630-542	Stahl	Cabinet Door	Steel Door, Perforated
21630-543	Stahl	Cabinet Door	Steel Door, Perforated
21630-544	Stahl	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE