

# Varistar CP Swing Frame for 600 mm Width

## Energieversorger

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

### EIGENSCHAFTEN

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

### SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Rack Height | Farbe      | Color Code | Höhe    | Material | Product Type       |
|---------------|-------------|------------|------------|---------|----------|--------------------|
| 21630-668     | 24 U        | Black Grey | RAL 7021   | 1200 mm | Stahl    | Cabinet/Rack Frame |
| 21630-670     | 29 U        | Black Grey | RAL 7021   | 1400 mm | Stahl    | Cabinet/Rack Frame |
| 21630-672     | 33 U        | Black Grey | RAL 7021   | 1600 mm | Stahl    | Cabinet/Rack Frame |
| 21630-674     | 38 U        | Black Grey | RAL 7021   | 1800 mm | Stahl    | Cabinet/Rack Frame |
| 21630-676     | 42 U        | Black Grey | RAL 7021   | 2000 mm | Stahl    | Cabinet/Rack Frame |
| 21630-678     | 47 U        | Black Grey | RAL 7021   | 2200 mm | Stahl    | Cabinet/Rack Frame |

Table 2/2

| Katalognummer | Protection Rating | Breite |
|---------------|-------------------|--------|
| 21630-668     | IP20              | 600 mm |
| 21630-670     | IP20              | 600 mm |
| 21630-672     | IP20              | 600 mm |
| 21630-674     | IP20              | 600 mm |
| 21630-676     | IP20              | 600 mm |
| 21630-678     | IP20              | 600 mm |

## ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**