

# Horizontal Pouring Basin, Top Fill, 90°



90 degree top fill horizontal pouring basins are used when structural interferences are directly above the tap hole in the sleeve.

## MERKMALE

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series horizontal top fill sleeves

## SPEZIFIKATIONEN

**Material:** Graphit

Table 1/1

| Katalognummer | Durchmesser (Ø) | Länge 1 (L1) | Länge 2 (L2) | Breite (W) | Höhe 1 (H1) | Höhe 2 (H2) |
|---------------|-----------------|--------------|--------------|------------|-------------|-------------|
| RB TSA9040X   | 38 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSA9735X   | 38 mm           | 248 mm       | 76 mm        | 76 mm      | 140mm       | 89mm        |
| RB TSA6040F   | 64 mm           | 152 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSA9740A   | 41 mm           | 248 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSA7040J   | 76 mm           | 179 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSA9040C   | 48 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |


| Katalognummer | Durchmesser (Ø) | Länge 1 (L1) | Länge 2 (L2) | Breite (W) | Höhe 1 (H1) | Höhe 2 (H2) |
|---------------|-----------------|--------------|--------------|------------|-------------|-------------|
| RB TSA9740C   | 48 mm           | 248 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSA9040D   | 54 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSB15045D  | 54 mm           | 381 mm       | 76 mm        | 76 mm      | 152mm       | 114mm       |
| RB TSB12040E  | 57 mm           | 305 mm       | 76 mm        | 76 mm      | 152mm       | 102mm       |
| RB TSA9040F   | 64 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSB12042F  | 64 mm           | 305 mm       | 76 mm        | 76 mm      | 152mm       | 108mm       |
| RB TSA9040J   | 76 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSB13545J  | 76 mm           | 342 mm       | 76 mm        | 76 mm      | 152mm       | 114mm       |
| RB TSA9040M   | 95 mm           | 229 mm       | 76 mm        | 76 mm      | 140mm       | 102mm       |
| RB TSB12050M  | 95 mm           | 305 mm       | 76 mm        | 76 mm      | 152mm       | 127mm       |
| RB TSB15045M  | 95 mm           | 381 mm       | 76 mm        | 76 mm      | 152mm       | 114mm       |
| RB TSB18550M  | 95 mm           | 470 mm       | 76 mm        | 76 mm      | 152mm       | 127mm       |
| RB TSC18550M  | 95 mm           | 470 mm       | 76 mm        | 76 mm      | 179mm       | 127mm       |
| RB TSC26050M  | 95 mm           | 660 mm       | 76 mm        | 76 mm      | 179mm       | 127mm       |

## ZUSÄTZLICHE PRODUKTDDETAILS

RB TSA pouring basins require one RBW341 pouring basin frame. RB TSB and RB TSC pouring basins require one RBW341 pouring basin frame and two RBS5000 bolt retainers (all sold separately).

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System Instruction Manual.

Sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.



## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

### Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

### Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Unser starkes markenportfolio:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**