

19" Pusher Fan, 2 U, Axial

Energieversorger

Fan tray with integrated pusher fan.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to subracks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Input Voltage AC	Input Voltage DC
10713-534	230 V min	
10713-518	230 V min	

Katalognummer	Input Voltage AC	Input Voltage DC
10713-526	230 V min	
10713-536	115 V min	
10713-520	115 V min	
10713-537		24 V min
10713-529		24 V min
19713-540		

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE