

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

KATALOGNUMMER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

MERKMALE

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUKTMERKMALE

Produkttyp: Schaltschranktür

Produktfamilie: Varistar CP

Typ: Stahltür, perforiert

Passt zu: Varistar CP

Verriegelungstyp: Einzelpunkt-Verriegelung

Farbe: Schwarzgrau

Farbcode: RAL 7021

Höhe Gestell: 29 U

Höhe: 1400 mm

Breite: 800 mm

Schutzart: IP20

Entspricht: IEC 61587-1

ZUSÄTZLICHE PRODUKTDDETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE