


EuropacPRO 19" Subrack Kit for DIN Connector

Energieversorger



Subrack for assembly to a wall or cabinet panel for Din connector mounting without rear hood.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type L ("light")

Internal and external dimensions in accordance with the IEC 60297-3-101 and IEEE 1101.1 standards

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

IP 20, in accordance with IEC 60529

For connector mounting (DIN 41612, EN 60602-3)

Horizontal rails type "light"

Aluminum construction

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Product Type	Rack Height	Rack Width	Tiefe	For Mounting	Board Depth
---------------	--------------	-------------	------------	-------	--------------	-------------

24563-109	Subrack/Chassis	3 U	28 HP	205 mm	DIN Connector	160 mm
-----------	-----------------	-----	-------	--------	---------------	--------

Table 2/2

Katalognummer	EMC Shielding	Statische Last	Handle Included	Montage	Konform mit	Package Quantity
24563-109	Nein	2.5 kgf	Nein	Wand	IEC 60297-3-103	1

ADDITIONAL PRODUCT DETAILS

EMC version on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE