


Novastar 19" Panel/Slide Mount

Energieversorger



Novastar 19" Panel/Slide Mount Kit with load capacity of 400 kg, ensures easy fitting of 19" components to depth members.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

For recessed installation of 19" components

For fitting to depth members (25 mm grid)

Load carrying capacity 400 kg

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Package Quantity	Farbe	Color Code	Höhe	Product Type
---------------	-------------	------------------	-------	------------	------	--------------

27230-172	6 U	1	Black Grey	RAL 7021	267.1 mm	Slide Mount
27230-173	9 U	1	Black Grey	RAL 7021	400.45 mm	Slide Mount
27230-174	12 U	1	Black Grey	RAL 7021	533.8 mm	Slide Mount
27230-175	16 U	1	Black Grey	RAL 7021	711.6 mm	Slide Mount
27230-176	20 U	1	Black Grey	RAL 7021	889.4 mm	Slide Mount
27230-177	25 U	1	Black Grey	RAL 7021	1111.65 mm	Slide Mount
27230-178	34 U	1	Black Grey	RAL 7021	1511.7 mm	Slide Mount
27230-179	38 U	1	Black Grey	RAL 7021	1689.5 mm	Slide Mount
27230-180	43 U	1	Black Grey	RAL 7021	1911.75 mm	Slide Mount
27230-181	47 U	1	Black Grey	RAL 7021	2089.55 mm	Slide Mount

Table 2/2

Katalognummer	Verpackungseinheit
27230-172	Paar
27230-173	Paar
27230-174	Paar
27230-175	Paar
27230-176	Paar
27230-177	Paar
27230-178	Paar
27230-179	Paar

Katalognummer	Verpackungseinheit
27230-180	Paar
27230-181	Paar

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE