

Varistar CP Double Steel Door, Perforated, 3-Point Locking

Energieversorger

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

EIGENSCHAFTEN

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-020	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-021	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-022	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-027	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-028	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-029	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-448	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-449	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-450	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-451	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-452	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-453	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-454	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-455	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Katalognummer	Locking Type	Product Type	Protection Rating	Typ	Kompatibel mit
21630-020	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-448	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-450	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-451	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

Katalognummer	Locking Type	Product Type	Protection Rating	Typ	Kompatibel mit
21630-452	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE