

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Energieversorger

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

EIGENSCHAFTEN

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Konform mit
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Katalognummer	Endbearbeitung	Locking Type	Material	Product Type	Protection Rating	Typ
21630-820	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Pulverbeschichtet	3-Point Locking, Electronic	Stahl	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Katalognummer	Kompatibel mit
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE