

Varistar CP Steel Door, Plain With 3-Point Locking and Brush Strip, Shortened

Energieversorger

Shortened door available for IP20, IP55 applications.

EIGENSCHAFTEN

Height of connection plate 400 mm

Connection plate with brush strip

The height of the door is 400 mm less than the cabinet height

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Locking Type
21630-348	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-349	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-350	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-351	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-352	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-353	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Katalognummer	Product Type	Protection Rating
---------------	--------------	-------------------

21630-348	Cabinet Door	IP20
21630-349	Cabinet Door	IP20
21630-350	Cabinet Door	IP20
21630-351	Cabinet Door	IP20
21630-352	Cabinet Door	IP20
21630-353	Cabinet Door	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE