


Cable Entry Gland Plate Connected Grommet Small, CCFGS



CCFGS cable glands are used with CCFI, CCFO and CCFR cable entry systems.

INDUSTRIE-STANDARDS

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

MERKMALE

IP66 Modular Halogen-free and silicone free cable entry system, that provide versatility, variability and variety

Everything mounted from the outside of the enclosure

The frames, inlays and grommets can be combined in many ways - ensuring you many versatile configuration options

The frame does not need to be disassembled if requirements change or carrying out service work

No need to disassemble and reconnect connectors on cables so manufactures warranty is not voided

The conical shape of the grommets allows them to be easily pressed in, provides static strain relief in accordance with DIN EN 62444

For assembly, they are pressed from the inside out into the openings of the assembled inlays

The grommets are available in different sizes to match the diameter of the cable

The CCFGS is first placed around the cable and then inserted into the cable gland

Based on the wave-cut profile, there is no need to remove the connector on the assembled cabled

SPEZIFIKATIONEN

Table 1/1						
Katalognummer	Höhe	Breite	Tiefe	Material	Oberfläche	Farbe
CCFGS15	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS14	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS12	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS13	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS10	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS11	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS8	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS9	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS6	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS7	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS2	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS4	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS5	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS015	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau
CCFGS3	20.3mm	20.3mm	17.7mm	Kunststoff	Unbehandelt	Grau

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.