

# nVent LENTON Interlok HY15LM Grout



The nVent LENTON Interlok HY15LM grout is a proprietary, nonmetallic, high-strength, nonshrink grout developed exclusively for the nVent LENTON Interlok coupling system. The nVent LENTON Interlok HY15LM grout is produced under strict nVent quality guidelines in order to ensure product quality along with consistent and reliable performance.

## ZERTIFIZIERUNGEN



## MERKMALE

Cures quickly, allowing early removal of bracing systems

Nonmetallic grout will not rust or stain structures

Designed to provide superior dynamic, seismic and ultimate strength performance for moment frame applications

For use in pump or gravity fill applications

## SPEZIFIKATIONEN

Table 1/1

| Katalognummer | Druckfestigkeit                  | Arbeitstemperatur | Stückgewicht |
|---------------|----------------------------------|-------------------|--------------|
| HY15LM        | 24.1 MPa @ 1 d, 110.3 MPa @ 28 d | 0 to 38 °C        | 22.68 kg     |

## ZUSÄTZLICHE PRODUKTDDETAILS

Compressive Strength is based on room temperature tests performed at 70°F (21°C).

The shelf life of nVent LENTON Interlok Grout is 12 months from the manufacturing date printed on the bag.

nVent LENTON Interlok Grout should be stored in a cool, dry environment. It is recommended that the nVent LENTON Interlok Grout be stored indoors to maintain maximum shelf life and physical properties.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

| Part Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Number of Couplers Per Bag of LENTON INTERLOK Grout |
|-------------|----------------|--------------------|----------------|--------------------|-----------------------------------------------------|
| LK5         | 145575         | 16 mm              | #5             | 15M                | 24                                                  |
| LK6         | 145580         | 20 mm              | #6             | 20M                | 25                                                  |
| LK7         | 145585         | 22 mm              | #7             | -                  | 26                                                  |
| LK8         | 145590         | 25 mm              | #8             | 25M                | 21                                                  |
| LK9         | 145595         | 28 mm              | #9             | 30M                | 17                                                  |
| LK10        | 145600         | 32 mm              | #10            | -                  | 13.5                                                |
| LK11        | 145605         | 36 mm              | #11            | 35M                | 11.5                                                |
| LK40        | 145610         | 40 mm              | -              | -                  | 7                                                   |
| LKT14       | 145611         | 43 mm              | #14            | 45M                | 7                                                   |
| LKT50       | 145615         | 50 mm              | -              | -                  | 4                                                   |
| LKT18       | 145620         | 57 mm              | #18            | 55M                | 4.5                                                 |

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

### Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

### Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Unser starkes markenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE