


Air Terminal Base, Stamped Adjustable, Imperial Thread

Power Utilities



MERKMALE

For use on flat, vertical or sloping surfaces

Air terminal support tab is field adjustable, eliminating the need for swivel adaptors

Available pre-configured for vertical applications

Install with adhesive or screw down fixings

Positive single bolt tension for multi-directional cable clamping

SPEZIFIKATIONEN


Table 1/1

Katalognummer	Leitergröße, UL	Höhe (H)	Breite (W)
LPA30212	Klasse 1 – Klasse 2 (4/0 max.)	34.92 mm	101.600 mm

ZUSÄTZLICHE PRODUKTDDETAILS

Vertical type bases are factory pre-configured for vertical mount applications.

DIAGRAMME



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE