

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Energieversorger

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Edelstahl
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Edelstahl
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Edelstahl
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Edelstahl
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Edelstahl
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Edelstahl
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl

Table 2/3

Katalognummer	Handle Included	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24563-191	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-192	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-193	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-194	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-491	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-492	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP
24563-493	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Katalognummer	HandleIncluded	Montage	Konform mit	EMC Shielding	Product Type	Rack Width
24563-494	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statische Last
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE