

# EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155, CompactPCI

## Energieversorger



Subrack for Railway applications, conform to EN50155 standard, for Compact PCI applications.

## ZERTIFIZIERUNGEN



## EIGENSCHAFTEN

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (toxic-welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additional safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Supplied as space-saving flat-pack

## SPEZIFIKATIONEN

Table 1/3

| Katalognummer | Rack Height | Package Quantity | For Mounting | Board Depth | EMC Gasket Type | Shock and Vibration Tolerance |
|---------------|-------------|------------------|--------------|-------------|-----------------|-------------------------------|
| 21500-081     | 3 U         | 1                | Backplane    | 160 mm      | Textile         | 5 g (force)                   |
| 21500-082     | 6 U         | 1                | Backplane    | 160 mm      | Textile         | 5 g (force)                   |

Table 2/3

| Katalognummer | Handle Included | Montage | Konform mit                                                        | Tiefe  | EMC Shielding | Product Type    |
|---------------|-----------------|---------|--------------------------------------------------------------------|--------|---------------|-----------------|
| 21500-081     | Ja              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, EN 50155 part 12.2.11 | 235 mm | Ja            | Subrack/Chassis |
| 21500-082     | Ja              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, EN 50155 part 12.2.11 | 235 mm | Ja            | Subrack/Chassis |

Table 3/3

| Katalognummer | Rack Width | Statische Last |
|---------------|------------|----------------|
| 21500-081     | 84 HP      | 15 kgf         |
| 21500-082     | 84 HP      | 15 kgf         |

## ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**