

Front Panel, Front Shielded, Side Hinged

Energieversorger

Front panel with textile EMC gasket, side hinged assembly.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for sub racks and cases

Hinges can be fitted on left or right

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Package Quantity	Montage	EMC Gasket Type	Front Finish	Rear Finish
20848-611	3 U	1	Hinged, Side	Textile	Anodized	Conductive
20848-617	6 U	1	Hinged, Side	Textile	Anodized	Conductive

Table 2/3

Katalognummer	Treated Edges	EMC Shielding	Höhe	Material	Product Type	Rack Width
20848-611	Nein	No (Retrofittable)	128.4 mm	Aluminium	Frontplatte	84 HP
20848-617	Nein	No (Retrofittable)	261.8 mm	Aluminium	Frontplatte	84 HP

Table 3/3

Katalognummer	Typ	Breite
20848-611	Front Panel without Handle	426.4 mm
20848-617	Front Panel without Handle	426.4 mm

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE