

Outdoor Unibody HEX

Energieversorger



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Double-walled, Al

Forced heat dissipation via integrated heat exchanger in the door, max. 70 W/K

IP 55

One-piece inner case with removable outer cladding

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Product Type	Product Family	Rack Height	Höhe	Breite	Tiefe
11249-016	Outdoorschrank	Unibody	25 U	1330 mm	700 mm	500 mm

Table 2/2

Katalognummer	Wall Type	Door Type	Zugang	Kühlung	EMC Shielding	Konform mit
11249-016	Double Walled	Single Door	Frontseitig	Air-to-Air Heat Exchanger	Nein	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE