

# RackPower Basic PDU, RB0xxx, 230 VAC, 1-phase

## Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

### MERKMALE

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Input connector IEC 60309 332P6

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### SPEZIFIKATIONEN

Table 1/2

| Katalognummer | Produkttyp    | Typ Buchse          | Farbe   | Länge   | Spannung AC | Tiefe |
|---------------|---------------|---------------------|---------|---------|-------------|-------|
| RB0328        | Buchsenleiste | IEC C13,<br>IEC C19 | Schwarz | 1490 mm | 230 V       | 53 mm |

Table 2/2

| Katalognummer | Breite |
|---------------|--------|
| RB0328        | 52 mm  |

### ZUSÄTZLICHE PRODUKTDDETAILS

Please order bracket for vertical mounting separately.

## WARNUNG

---

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**