

Varistar CP Steel Door, Glazed With 3-Point Locking, Shortened

Energieversorger

Shortened door available for IP20, IP55 applications.

EIGENSCHAFTEN

Glazed door

Height of connection plate 400mm

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Rack Height	Höhe	Breite	Farbe	Color Code	Locking Type
21630-346	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-342	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-345	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-344	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-347	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-343	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Katalognummer	Product Type	Protection Rating
21630-346	Cabinet Door	IP20

Katalognummer	Product Type	Protection Rating
21630-342	Cabinet Door	IP20
21630-345	Cabinet Door	IP20
21630-344	Cabinet Door	IP20
21630-347	Cabinet Door	IP20
21630-343	Cabinet Door	IP20

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE