

2000 U-Channel



FEATURES

Light duty U-channel for use with 2000 series beam clamps


SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2								
Catalog Number	Article Number	Length (L)	Height (H)	Width (W)	Thickness (T)	Hole Size (HS)		
2006EG	570350	400mm	12 mm	25 mm	2 mm	11 mm		
2002EG	570310	200mm	12 mm	25 mm	2 mm	11 mm		

Table 2/2								
Catalog Number	Article Number	X	A	В				
2006EG	570350	8.5 x 25 mm	30.5 mm	25 mm				
2002EG	570310	8.5 x 25 mm	30.5 mm	25 mm				



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

