

# **DUPLO NI Double Pipe Clamp**



## **FEATURES**

Fast installation of parallel pipes from a single anchor

Height adjustable

## **SPECIFICATIONS**

Finish: Electrogalvanized


Material: Steel


Table 1/2								
Catalog Number	Article Number	Outer Diameter (OD)	NB/DN	Width (W)	Thickness (T)	A		
DUPLON22EG	596041	22 mm	15	20 mm	1.5 mm	60 mm		
DUPLON28EG	596042	28 mm	20	20 mm	1.5 mm	60 mm		
DUPLON15EG	596040	15 mm		20 mm	1.5 mm	60 mm		

Table 2/2								
Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)					
DUPLON22EG	596041	6	16mm					
DUPLON28EG	596042	6	16mm					

Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)
DUPLON15EG	596040	6	16mm

## **DIAGRAMS**





#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO S

SCHROFF

TRACHTE



nVent.com/CADDY 2

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.