

nVent CADDY Pyramid H-Frame Kit



CERTIFICATIONS



FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Kit includes 2 post bases with pre-installed mounting hardware, 6 bolts, 6 strut nuts, and 2 L-brackets to complete H-frame
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels

SPECIFICATIONS

Static Load Safety Factor:	3:1
Material:	Polypropylene;Polyethylene
Temperature:	-34.4 to 54 °C

Table 1/2

Catalog Number	Article Number	Rooftop Interface	Strut Type	Height (H)	Length (L)	Width (W)
----------------	----------------	-------------------	------------	------------	------------	-----------

PHK	360420	Foam	A (41 x 41 mm)	117 mm	314mm	314 mm
PHKR	360421	Rubber	A (41 x 41 mm)	118 mm	314mm	314 mm

Table 2/2

Catalog Number	Article Number	Surface Area	Static Load
PHK	360420	0.18m ²	6670N
PHKR	360421	0.2m ²	6670N

ADDITIONAL PRODUCT DETAILS

Static load represents 750 lb (3,335 N) per post base. The end user must select and evaluate the strut framing to ensure the assembled H-frame can properly support the applied load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

