

Socket Strip, SCHUKO

Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

CERTIFICATIONS



FEATURES

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFICATIONS

Material: Aluminum; Polyamide

Color: Grey

Product Type: Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-200	SCHUKO	3	No	230V		1
60110-201	SCHUKO	4	No	230V		1
60110-202	SCHUKO	9	No	230V		1
60110-206	SCHUKO	8	Yes	230V		1
60110-210	SCHUKO	8	No	230V	Transient Protection	1
60110-214	SCHUKO	7	No	230V	Mains Suppression Filter	1
60110-266	SCHUKO	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-203	SCHUKO	12	No	230V		1
60110-204	SCHUKO	15	No	230V		1
60110-205	SCHUKO	19	No	230V		1
60110-207	SCHUKO	12	Yes	230V		1
60110-208	SCHUKO	15	Yes	230V		1
60110-209	SCHUKO	19	Yes	230V		1
60110-211	SCHUKO	9	No	230V	Transient Protection	1
60110-212	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-216	SCHUKO	6	No	230V	Fault Current Protection	1

CatalogNumber	Socket Type	SocketQuantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-217	SCHUKO	6	No	230V	Fault Current Protection, Overcurrent Protection	1

Table 2/2

Catalog Number	Depth	Finish	Length
60110-200	44mm	Anodized	184mm
60110-201	44mm	Anodized	210mm
60110-202	44mm	Anodized	438.5mm
60110-206	44mm	Anodized	438.5mm
60110-210	44mm	Anodized	438.5mm
60110-214	44mm	Anodized	438.5mm
60110-266	44mm	Anodized	438.5mm
60110-203	44mm	Anodized	947.5mm
60110-204	44mm	Anodized	1202mm
60110-205	44mm	Anodized	1753mm
60110-207	44mm	Anodized	947.5mm
60110-208	44mm	Anodized	1202mm
60110-209	44mm	Anodized	1753mm
60110-211	44mm	Anodized	947.5mm
60110-212	75mm	Anodized	438.5mm

Catalog Number	Depth	Finish	Length
60110-216	88mm	Anodized	438.5mm
60110-217	88mm	Anodized	438.5mm

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE