

Varistar CP Glazed Door With 1-Point Locking

Data Solutions



Varistar CP Glass Door Single Point Locking for IP 20 applications.

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel; Glass

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-016	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-017	42U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-018	47U	2000mm	800mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-019	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-392	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-393	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-394	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-395	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-396	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-397	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-398	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-399	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-481	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-482	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-483	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-484	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-485	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-486	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-487	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-488	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-489	42U	2000mm	600mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-490	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-491	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-492	47U	2200mm	800mm	Single Point Locking	1	Black Grey

Table 2/2					
Catalog Number	Color Code	Complies With	Finish	Type	Works With
21630-016	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-017	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-018	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-019	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-392	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-393	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-394	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-395	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-396	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-397	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-398	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-399	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-481	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-482	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP

Catalog Number	Color Code	Complies With	Finish	Type	Works With
21630-483	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-484	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-485	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-486	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-487	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-488	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-489	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-490	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-491	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP
21630-492	RAL 7021	IEC 61587-1	Powder Coated	Glass Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE