

Crimping Compression Tool, Foot Pump



FEATURES

Wide cross section range

High-pressure 2 meter (6.5') long hose

Compact and easy to use

Includes easy-to-carry custom case

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Applied Force	System	Dies	Crimping Shape	Conductor Size
M4FP	716925	250kN	Foot pump hydraulic	PKM4 series	Hexagon	#6 Stranded - 1000 kcmil Stranded, 16 mm ² Stranded - 625 mm ² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE