

Earth Seal Flange



SPECIFICATIONS

Table 1/3

Catalog Number	Material	Color	Length	Width	Diameter 1	Diameter 2
ESA308	Polypropylene, Polyethylene	Black	308mm	308 mm	366 mm	290 mm

Table 2/3

Catalog Number	Diameter 3	Height	Depth	Water Pressure	Complies With	Working Load
ESA308	50mm	214 mm	2300mm	5 t	EN IEC® 62561-5	5bar

Table 3/3

Catalog Number	Unit Weight
ESA308	6 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE